



orange 1	green 2
white/orange	white/green
blue 3	brown 4
white/blue	white/brown



Conductor	Bare Copper 26AWG 7/0.152±0.005mm
Insulation	Thickness:MIN at any point:0.2mm MAX AVG:0.35mm Diameter:1.05±0.05mm
Jacketing	LSOH Thickness:MIN at any point:0.46mm MAX AVG:0.58mm Diameter:6.1±0.2mm

WIRE	CAT.6 PIMF STR 26AWG LSOH
PLUG	YUS-06

PA/R	PINOUT		
	P1 (T568B)	WIRE	P2 (T568B)
1	1	WHT/ORG	1
	2	ORG	2
2	3	WHT/GRN	3
	6	GRN	6
3	4	BLU	4
	5	WHT/BLU	5
4	7	WHT/BRN	7
	8	BRN	8


color/length index

length	color	item no.	length	color	item no.
0,25 m	white	605513	1,00 m	red	605520
1,00 m	white	605510	1,00 m	yellow	605560
7,5 m	white	605515	1,00 m	blue	605630
15 m	white	605518	1,00 m	green	605640
20 m	white	605519	0,50 m	color x	6055x7
30 m	white	605530	2,00 m	color x	6055x1
40 m	white	605540	3,00 m	color x	6055x3
50 m	white	605550	5,00 m	color x	6055x4
			7,5 m	color x	6055x5
			10 m	color x	6055x6
			15 m	color x	6055x8
			20 m	color x	6055x9

white (x=1), red (x=2), blue (x=3), green (x=4), yellow (x=6), orange (x=7), black (x=9)

Unless specified on the drawing, tolerances are per the follows:
 . ± 1
 .X ± 0.2
 .XX ± 0.05





Patchkabel Cat.6 S/FTP

3RD	UNIT	MM	SHEET	1	OF	1
-----	------	----	-------	---	----	---