


3-Pin Threaded M8/Pico-Style Splitter Cordset—Flat Junction

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass (female) and nylon/nickel-plated brass (male) coupling nuts
Conductors: 24 AWG, gold-plated contacts
Voltage/Current Rating: 125V ac/dc, 4.0 A
Temperature: -40° to +105° C **Environmental Rating:**
Wiring: Parallel wired Y-cords



Connections

Model	Branches	Trunk	Cable Diameter	Pinout	Used With
CSB-M831M831	3-Pin Pico QD 2 x 0.20 m Female	0.20 m Male	4.40 mm	Female  Male  1 = Brown 3 = Blue 4 = Black	<ul style="list-style-type: none"> Connect P4 to two lights Spot Lights Area Lights Backlights
Dimensions (mm)					
					

3-Pin M8/Pico-Style and 4-Pin M12/Euro-Style to Flying Leads Splitter Cordset—Flat Junction




Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut
Conductors: 24 AWG (3-pin) or 22 AWG (4-pin), gold-plated contacts
Voltage/Current Rating: 250V ac/300V dc, 4.0 A
Temperature: -40° to +105° C **Environmental Rating:** IP67

Connections

Model	Branches	Trunk	Cable Diameter	Pinout	Used With
CSB-UNT213M831F1241	3-Pin Pico QD 0.3 m Male 4-pin Euro QD 0.3 m Female	Flying Leads 4 m	4.40 mm (branches) 5.50 mm (trunk)	Female  1=Brown 2=White 3=Blue 4=Black Male  1 = NC 3 = Blue 4 = Black	<ul style="list-style-type: none"> P4 to High Intensity Area Lights (to strobe from P4)
Dimensions (mm)					
					

4-Pin Snap-on M8/Pico-Style Cordsets

Cable: PVC jacket, PUR (polyurethane) connector body, nylon coupling nut
Conductors: 26 AWG, gold-plated contacts
Voltage/Current Rating: 125V ac/dc, 2.0 A
Temperature: -40° to +90° C **Environmental Rating:** IP67

Style	Length	Model	Cable Diameter	Dimensions (mm)	Pinout	Used With
Straight	2.00 m	PKG4-2	3.20 mm		Female  1 = Brown 2 = White 3 = Blue 4 = Black	<ul style="list-style-type: none"> QS18 Q20 D12 D10A S12
Right-Angle	2.00 m	PKW4Z-2	3.20 mm		Female  1 = Brown 2 = White 3 = Blue 4 = Black	