

Cable cutters with double cutting edge

For diameters up to 20 mm, with 2-component grip covers



Application:

For cutting single and multi-conductor copper and aluminium cables.

Execution:

- Special-grade tool steel, forged, oil-hardened
- Hardened, precision-ground blades
- Not suitable for steel wire and hard-drawn copper wire
- Adjustable screw joint, self-locking

Advantage:

- Safe, ergonomic and fatigue-free working thanks to two-component handles
- Cuts smoothly and cleanly without crushing
- Pinch guard prevents crushing injuries
- Low force required thanks to favourable transmission ratios and optimised blade geometry
- By splitting the cutting process into pre-cut (insulating sheath with front blade area) and post-cut (conductor in rear blade area), cables up to 20 mm in diameter can be cut with one hand



Art. no.	53100 105
Brand	KNIPEX
Manufacturer Part Number	95 12 200
Length	200 mm
Max. medium wire diameter cutting capacity	20 mm
Surface	Plain
Material of handle	2-component plastic
Gross Weight	0.330 kg
Product Group	535

EAN

4003773047834