

**Clamping yoke  
KLBUE 3-8 SC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The electromagnetic compatibility (EMC) of electrical machines and installations has become a very important aspect. Weidmüller is facing up to this challenge with the KLBÜ shield connection terminals. These are available in different versions.

**General ordering data**

Type	KLBUE 3-8 SC
Order No.	<a href="#">1692261001</a>
Version	Clamping yoke, Clamping yoke, Steel, 18 mm
GTIN (EAN)	4032248032365
Qty.	10 pc(s).

## Data sheet

### Clamping yoke KLBUE 3-8 SC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Length	18 mm	Width	14 mm
Height	26 mm	Net weight	10.794 g

### Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

### Additional technical data

Explosion-tested version	No	Installation advice	Busbar
Version	For a shield connection		

### Wire clamp for cable diameter

Cable diameter, min.	3 mm	Cable diameter, max.	8 mm
----------------------	------	----------------------	------

### Material data

Material	Steel
----------	-------

### System specifications

Product family	Clamping yoke
----------------	---------------

### Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 6.2	27-14-11-90	eClass 7.1	27-14-11-50

### Approvals

ROHS	Conform
------	---------