



LED LAMP, ULTRA-BRIGHT, BLUE, RATED VOLTAGE AC/DC 24V, WEDGE-BASE W2 X 4.6D



Figure similar

General technical data:		
Product designation		LED lamp, super bright
Type of light source		LED
Color of the light source		blue
Mounting type		W2 x 4.6d
Product component		
• series resistor		No
• diode		No
• lamp transformer		No
• Light source		Yes
Type of voltage for actuation		AC/DC
Operating voltage		
• with AC		
— at 50 Hz Rated value	V	24 ... 24
— at 60 Hz Rated value	V	24 ... 24
• for DC Rated value	V	24 ... 24
Consumed current for rated value of supply voltage maximum	mA	10
Type of electrical connection		Miscellaneous
Mounting type		miscellaneous

Certificates/ approvals:

General Product Approval	Declaration of Conformity	Test Certificates	other
 CSA	 UL	 EAC	 EG-Konf.
		Special Test Certificate	Confirmation

other	
other	Environmental Confirmations

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB29081BD>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SB29081BD/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3SB29081BD&lang=en>

last modified:

09.03.2015