



Identification	Series	Part number		Contact arrangement view termination side	Dimensions in mm
		Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately	Han E®				
	6 E	09 33 006 2602	09 33 006 2702		
	10 E	09 33 010 2602	09 33 010 2702		
	16 E	09 33 016 2602	09 33 016 2702		
	24 E	09 33 024 2602	09 33 024 2702		
Crimp terminal Order crimp contacts separately	Han® Q				
		09 12 005 3001	09 12 005 3101		
Crimp terminal Order crimp contacts separately	Han A®				
		10 A	09 20 010 3001		
	16 A	09 20 016 3001	09 20 016 3101		
Identification	Wire gauge (mm²)	Male contact	Female contact	Drawing	Dimensions in mm
Crimp contacts Han E® Constantan Iron; gold plated Standard contacts; silver plated 	0.14-0.37 0.5	09 33 000 6163	09 33 000 6263		
		09 33 000 6162	09 33 000 6262		
	0.14-0.37 0.5	09 33 000 6173	09 33 000 6273		
		09 33 000 6172	09 33 000 6272		
	0.5 0.75 1 1.5 2.5 4	09 33 000 6121	09 33 000 6220		
		09 33 000 6114	09 33 000 6214		
		09 33 000 6105	09 33 000 6205		
		09 33 000 6104	09 33 000 6204		
		09 33 000 6102	09 33 000 6202		
		09 33 000 6107	09 33 000 6207		

Dimensions for inserts see chapter of corresponding series

Stock items in bold type