

Steckhülsen 6,3 mm

Clips femelles

Receptacles


DIN 46247/3

* ausgenommen
* excepté
* excepted

Werkstoff/Matière/Material
.2 = Bronze/bronze
.6 = Messing/laiton/brass
.9 = Stahl/acier/steel

■ = Oberflächen/Surface/Surface-plating
Seite/page/page 5.011


Strombelastbarkeit / Intensité admissible / Current carrying capacity:
0.5 – 1.0 mm² / 10A max.
1.5 – 2.5 mm² / 15A max.
4.0 – 6.0 mm² / 25A max



| mm ² | AWG | Grösse Grandeur Size | Artikelnummer Numéro d'article Part-No. | DIN | L1 mm | L2 mm | L3 mm | A1 mm | A2 mm | S mm | Werkzeuge Outils Toolings |
|-----------------|-------|----------------------------|---|----------|----------|----------|----------|----------|----------|---------|---|
| 0.5-1 | 22-18 | 6.3 x 0.8 | 3831.6 ■ | 46247/T3 | 19 | 7.5 | 4 | 8.3 | 4.5 | 0.45 | 3983p.4, 3984a, 3988n |
| | 22-18 | 6.3 x 0.8 | 3831.9 ■ | 46247/T3 | 19 | 7.5 | 4 | 9 | 4.5 | 0.45 | |
| 0.5-1.5 | 22-16 | 6.3 x 0.8 | 3832.6 ■ | 46247/T3 | 19 | 7.5 | 4 | 9 | 4.5 | 0.45 | 3983p.4, 3984a, 3988n |
| | 22-16 | 6.3 x 0.8 | 3832.9 ■ | 46247/T3 | 19 | 7.5 | 4 | 9 | 4.5 | 0.45 | |
| 1-2.5 | 18-14 | 6.3 x 0.8 | 3833.2 ■ | 46247/T3 | 19 | 7.5 | 4 | 8.5 | 4 | 0.4 | 3975c, 3983p.4, 3984a, 3988n |
| | 18-14 | 6.3 x 0.8 | 3833.6 ■ | 46247/T3 | 19 | 7.5 | 4 | 8.5 | 4 | 0.4 | |
| | 18-14 | 6.3 x 0.8 | 3833.9 ■ | 46247/T3 | 19 | 7.5 | 4 | 8.5 | 4 | 0.4 | |
| 4-6 | 12-10 | 6.3 x 0.8 | 3835a.6 ■ | 46247/T3 | 19 | 7.5 | 4 | 9 | 4.5 | 0.45 | 3975c, 3983p.4, 3984b, 3988n |

Werkstoff/Matière/Material
.6 = Messing/laiton/brass


■ = Oberflächen/Surface/Surface-plating
Seite/page/page 5.011



| mm ² | AWG | Grösse Grandeur Size | Artikelnummer Numéro d'article Part-No. | DIN | L1 mm | L2 mm | L3 mm | A1 mm | A2 mm | S mm | Werkzeuge Outils Toolings |
|-----------------|-------|----------------------------|---|----------|----------|----------|----------|----------|----------|---------|---|
| 1-2.5 | 18-14 | 6.3 x 0.8 | 3832d.6 ■ | 46340/T3 | 19 | 7.5 | 7.3 | 8.5 | 4 | 0.4 | 3975c, 3983p.4, 3984a, 3988n |

Werkstoff/Matière/Material
.6 = Messing/laiton/brass
.9 = Stahl/acier/steel

■ = Oberflächen/Surface/Surface-plating
Seite/page/page 5.011



| mm ² | AWG | Grösse Grandeur Size | Artikelnummer Numéro d'article Part-No. | DIN | L1 mm | L2 mm | L3 mm | A1 mm | A2 mm | S mm | Werkzeuge Outils Toolings |
|-----------------|-------|----------------------------|---|----------|----------|----------|----------|----------|----------|---------|---|
| 4-6 | 12-10 | 6.3 x 0.8 | 3835.6 ■ | 46247/T3 | 19 | 7.5 | 4 | 9 | 4.5 | 0.45 | 3975c, 3983p.4, 3984b, 3988n |
| | 12-10 | 6.3 x 0.8 | 3835.9 ■ | 46247/T3 | 19 | 7.5 | 4 | 9 | 4.5 | 0.45 | |