

Product information

98 25 00

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

Screwdriver for cross recessed screws

Pozidriv®

IEC 60900 DIN EN 60900



⚠ 1000 V ⚡

| General | |
|-------------------------------|---|
| Article No. | 98 25 00 |
| EAN | 4003773062370 |
| point | burnished |
| Handles | insulating multi-component handle, VDE-tested |
| Weight | 32 g |
| Dimensions | 162 x 25 x 25 mm |
| Standard | DIN EN 60900 IEC 60900 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |
| Technical details | |
| Size | PZ0 |
| Blade length | 60 mm |
| Handle length | 102 mm |
| Blade Ø | 3.0 mm |
| Length of non-insulated blade | 15 mm |
| VDE tested | yes |

technical change and errors excepted

Pozidriv® is a registered trademark of European Ind. Serv. Ltd.