

LED magnifying lamp varioLED flex

ESCHENBACH

Application:

For magnifying small parts with additional light source.

Execution:

- Illuminance: approx. 6000 lx (at 150 mm working distance)
- Mounted with a table clamp for table thicknesses up to 60 mm
- Switch between ring and segment illumination
- illumination near point for shadow-free lighting: 35 mm
- Gooseneck stand
- Comfortable alignment of magnifying lamp with ergonomic magnifier handle
- PXM plastic lightweight lens

Advantage:

- calculated optical light guidance for shadow-free ring lighting with 63 SMD LEDs, even at extremely low working distances

Delivery:

including mains adapter (adapter for EU, GB, US) and table clamp



Art. no.	41325 100
Magnification	2,5-times
Lens diameter	76 mm
Tripod length	350 mm
Lens design	Aspherical
Material of lens	Plastic light lens with scratchproof cera-tec® hard coating
Design	Swan neck with table clamp
Product Group	Prod. Gr. 4AA

EAN

4048347393764