

Product specification sheet

Revision dated March 2023

1.	Product code	275RP/**									
2.	Product description	13 gauge green cut resistant sandy nitrile coated glove									
3.	Material	HPPE, recycled polyester, glass fiber, steel									
4.	Coating	Sandy nitrile (palm)									
5.	Glove dimensions, codes and length	Dimensions		Size							
		XS 6	S 7	M 8	L 9	XL 10	XXL 11	XXXL 12			
		Product code	275RP/06	275RP/07	275RP/08	275RP/09	275RP/10	275RP/11	-		
		Length (mm)	220	230	240	250	260	270	-		
6.	Glove standards	EN388	Level		EN407	Level					
		Abrasion	4		Limited flame spread (burning behaviour)	-					
	Coup cut	X		Contact heat	-						
	Tear	4		Convective heat	-						
	Puncture	3		Radiant Heat	-						
	ISO cut	F		Small splashes of molten metal	-						
	Impact	-		Large splashes of molten metal	-						
	EN511	Level		EN60903							
	Convective cold	-		Arc flash	-						
	Contact cold	-		Type	-						
Water resistance	-		Mechanical	-							
	EN374 type	-									
7.	Thickness (mm)	n/a									
8.	Gauge	13									
9.	Cuff type	Knitted									
10.	Design	Hand specific									
11.	Surface	-									
12.	Colour	Green / black									
13.	Quality assurance	Manufactured under ISO 9001									
14.	Shelf life	5 years									
15.	Standards compliant with	EN388	EN407	EN511	EN 60903	EN420	EN374-1	EN374-2	EN374-4	EN374-5	Food approved
		✓				✓					
16.	Technologies	NitreGrip®			✓	NitreGuard®		✓	Oeko-Tex® Standard 100		✓

The above data represents the product norm, which may be changed without notice and is intended as a guide only.