

CASES 1200 Case



Peli protector cases - Watertight protector cases - 1200 case



Interior dimensions:
23.5 x 18.1 x 10.5 cm (9" x 7" x 4")

Watertight, crushproof, and dust proof

- Easy-open, double-step latches
- Open cell core with solid wall design - strong, light weight
- O-ring seal
- Automatic Pressure Equalization Valve
- Stainless steel hardware
- Pick 'N' Pluck™ with convoluted lid foam
- Unconditionally Guaranteed

Peli protector cases - Watertight protector cases - 1200 case SPECIFICATIONS

Exterior Dimensions (L x W x D)	Interior Dimensions (L x W x D)
27 x 24.6 x 12.4 cm (11" x 10" x 5")	23.5 x 18.1 x 10.5 cm (9" x 7" x 4")

Lid Depth	Bottom Depth	Total Depth
3 cm (1")	7.4 cm (2.93")	10.4 cm (4.11")

Lid Depth	Bottom Depth	Total Depth
3 cm (1.18")	7.4 cm (2.93")	10.4 cm (4.11")

Weight w/Foam	Weight w/o Foam	Buoyancy Max.
1.3 kg. (2.87 lbs)	1.2kg (2.65 lbs.)	5.45 kg (12.02 lbs.)

Range Temperature
-40 / 99° C (-40 / 210° F)

1200 Case Certificates

- IP67(1 meter submersion for 30 minutes)
- Def Stan 81-41/STANAG 4280

Materials

Body	Latch	Lid O-Ring	Pins
Polypropylene	ABS	PolymerStainless Steel	

Foam	Purge Body	Purge Vent	Purge O-Ring
1.3 lb Polyurethane	ABS	3 Micron Hydrophobic Non- Woven PET	70 Shore Nitrile

Configuration

Cat. #	Description
1200	Peli protector cases - Watertight protector cases - 1200 case
1200NF	1200 Case (no foam)

Peli protector cases - Watertight protector cases - 1200 case Accessories

Cat. #	Description
1201	3 pc. Replacement Foam Set
1203	Replacement O-ring
1200PF	Special Application Panel Frame