




ENCLOSURES 
Right Now, Right Price.



NEMA Boxes








UL/NEMA/IEC NBB Series



Most of these gasketed enclosures have been tested and approved to UL508-4x specifications, with a few being approved to UL50-4x. All enclosures meet NEMA 1, 4, 4x and IEC529-IP66 requirements, which allows them to be used in many wet, dirty and/or corrosive environments.

Design Features

- Designed to IP66 of IEC 529 and NEMA 1, 4 and 4x specifications.
- UL Listed to UL508-4x requirements
- **Indoor Versions:**
 - ABS plastic enclosures are molded out of light gray material with UL94-HB flammability rating. (Not UL Listed)
 - ABS/PC blended plastic enclosures are molded out of light gray material with UL94-5VA flammability rating. Suggested service temperature range -40C to +70C.
 - Clear doors, for all models, are molded out of polycarbonate material with UL94-V0 flammability rating
- **Outdoor Versions:**
 - *PC/PBT blended plastic enclosures are molded out of light gray material with UL94-5VA flammability rating and UV stabilized
- **Economy Versions:**
 - ABS plastic enclosures are molded out of light gray material with UL94-HB flammability rating. (Not UL Listed)
 - All plastic construction

PLASTIC BOXES - NBB SERIES													
ABS Version Catalog Number**	UL508-4X Indoor Version		UL508-4X Outdoor Version		Dwgs.	External Dimensions				Internal Dimensions			Wgt. Lbs.
	Catalog Number		Catalog Number			A	B	C	D	E	F	G	
	Solid Door	Clear Door	Solid Door	Clear Door									
NBB-22220#	NBB-10220#	NBB-10230#	N/A	N/A	OBS	5.11"	3.94"	2.75"	1.96"	4.37"	3.18"	2.53"	0.5
NBB-22221#	NBB-10221#	NBB-10231#	N/A	N/A	OBS	5.90"	3.94"	2.75"	1.96"	5.11"	3.18"	2.53"	0.6
NBB-22222#	NBB-10222#	NBB-10232#	N/A	N/A	OBS	7.87"	3.94"	2.75"	1.96"	7.08"	3.18"	2.53"	0.7
NBB-22223#	NBB-10223#	NBB-10233#	N/A	N/A	OBS	10.63"	3.94"	2.75"	1.96"	9.88"	3.18"	2.53"	1.1
NBB-22240	NBB-10240	NBB-10260	NBB-15240	*		5.90"	5.90"	3.57"	2.75"	5.04"	5.04"	3.27"	1.2
NBB-22241	NBB-10241	NBB-10261	*	*		10.73"	6.79"	4.33"	3.15"	9.84"	5.90"	4.07"	1.7
NBB-22243	NBB-10243	NBB-10263	NBB-15243	*		11.28"	7.47"	5.50"	4.33"	10.46"	6.65"	5.25"	2.2
NBB-22245	NBB-10245	NBB-10265	NBB-15245	*		13.00"	13.00"	7.04"	5.86"	12.14"	12.14"	6.79"	4.4
NBB-22247	NBB-10247	NBB-10267	NBB-15247	*		15.68"	11.73"	6.30"	5.11"	14.88"	10.89"	6.03"	4.2
NBB-22251	NBB-10251	NBB-10271	*	*		14.52"	10.55"	5.90"	4.72"	13.74"	9.76"	5.64"	3.5
NBB-22253	NBB-10253	NBB-10273	NBB-15253	*		19.17"	14.64"	7.85"	6.67"	18.33"	13.75"	7.60"	6.6
NBB-32640#	N/A	N/A	N/A	N/A	OBS	5.90"	5.90"	3.57"	2.76"	5.30"	5.30"	3.35"	0.8
NBB-32643#	N/A	N/A	N/A	N/A	OBS	11.28"	7.47"	6.30"	5.12"	10.85"	6.91"	6.09	2.8
NBB-32647#	N/A	N/A	N/A	N/A	OBS	15.68"	11.73"	6.30"	5.12"	14.75"	10.81"	6.09"	5.6
NBB-32653#	N/A	N/A	N/A	N/A	OBS	19.17"	14.64"	6.30"	5.12"	18.76"	14.74"	6.06"	9.6

* Contact factory for quotation. ** Not UL Listed. N/A = Not Available
 # Discontinued items. See table below for possible substitution

NBB SERIES OBSOLETE PARTS SUBSTITUTION GUIDE

Obsolete Part Number	Suggested Replacement Part	Obsolete Part Number	Suggested Replacement Part	Obsolete Part Number	Suggested Replacement Part	Obsolete Part Number	Suggested Replacement Part
NBB-10220	NBF-32102	NBB-10231	NBF-32204	NBB-15258	NBF-32346	NBB-22258	NBF-32046
NBB-10221	NBF-32104	NBB-10232	NBF-32206	NBB-22220	NBF-32002	NBB-32640	NBF-32010
NBB-10222	NBF-32106	NBB-10233	NBF-32208	NBB-22221	NBF-32004	NBB-32643	NBF-32018
NBB-10223	NBF-32108	NBB-10258	NBF-32146	NBB-22222	NBF-32006	NBB-32647	NBF-32026
NBB-10230	NBF-32202	NBB-10278	NBF-32246	NBB-22223	NBF-32008	NBB-32653	NBF-32032