


Vandal-Proof Pushbutton Switch



Specification

Button Material	Al Alloy
Contact Material	Silver Alloy
Base Material	PC
Body Material	Stainless Steel
Terminal Material	Brass, Silver Plated
Contact Rating	16 A, 125 / 250 VAC
Electrical Life	10000 Cycles min. at Full Load
Dielectric Strength	1500 VAC for 1 min.
Contact Resistance	300 mOhm max.
Operating Temperature Min.	-30 °C
Operating Temperature Max.	85 °C
Switch Function	OFF-(ON)
Insulation Resistance	100 MOhm min, 500 VDC
Contact Configuration	SPST Momentary
Illumination	No Illumination
Bushing Diameter	22 mm
IP Rating	IP65
Termination Type	Quick Connect
Button Type	Flat

Drawing



Art. Nr.
RND 210-006&1