



**NOTE:**

- Electrical test:
  - 100% open short & miss wire test;
  - Insulation resistance:DC 300V 0.01s 10M ohm min;
  - Contact resistance:8 ohm max;
- Computer + Monitor test
  - Resolution:3840\*2160@60Hz
- Marking:Display Port Cable AWM STYLE 20276 80°C 30V VW-1
- RoHS3.0 and REACH Compliant
- PACKING:1pc/Synergy 21 A bag+label
- Operating Temperature:0°C~45°C / Storage Temperature:-20°C~ 70°C  
Operation humidity:10%~85% / Storage humidity:10%~85%

**MATERIAL LIST:**

NO.	PARTS NAME	SPECIFICATION DESCRIPTION	QT' Y	REMARK
⑥	Dust Cap	LD PE	2	
⑤	TUBE END	BLACK PVC 45P	2	
④	INNER COVER	LD PE	2	
③	OUTER COVER	DP 20PIN MALE BLACK ABS ASSEMBLY TYPE	2	
②	CONNECTOR	DP 20P/M WITH LATCHING SOLDER TYPE, BLACK INSULATION, THE PIN GOLD PLATED, THE SHELL FOR Gold PLATED	2	
①	CABEL	[(30AWG CCS)*1P+D+FAM]*5+(30AWG CCS)+HDPE*4C+AD PVC/BLACK JACKET, OD:5.5±0.2MM	1	

ITEM NO	LENGTH
S215437V2	500 ± 30mm
S215438V2	1000 ± 30mm
S215439V2	1500 ± 50mm
S215440V2	2000 ± 50mm
S215441V2	3000 ± 70mm

SYNERGY21				
NO.	PARTS NAME	SPECIFICATION DESCRIPTION	QT' Y	REMARK
		NEW	2022-09-09	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

CUSTOMER		ITEM NO.	
PRODUCT NAME	30AWG CCS DisplayPort 1.2V Male-Male Gold plating	manufacture country:	CHINA
DRAWNBY	CHECKBY	APPOBY	DATE
SYNERGY21	SYNERGY21	SYNERGY21	2022-09-09