



Mechanical characteristics

cables

interface dimensions acc. to assembly code
 centre conductor
 outer conductor
 mating life

Components

centre contact
 outer contact
 other metal parts
 crimp ferrule
 insulator
 gasket

Electrical characteristics

impedance
 return loss
 working voltage
 voltage proof
 insulation resistance
 contact resistance
 centre contact
 outer contact

Environmental

operating temp.
 RoHS compliant

Mechanische Eigenschaften

Kabel

Steckgesicht nach Montageanleitung
 Innenleiter
 Außenleiter
 Steckzyklen

Bauteile

Innenkontakt
 Außenkontakt
 sonstige Metallteile
 Crimprohr
 Isolierung
 Dichtung

Elektrische Eigenschaften

Wellenwiderstand
 Rückflussdämpfung
 Betriebsspannung
 Prüfspannung
 Isolationswiderstand
 Durchgangswiderstand
 Innenkontakt
 Außenkontakt

Umgebung

Betriebstemperatur
 RoHS konform

G39 (0,8/3,7-6,15): 0,8/3,7 AF Draka; 0,8/3,7C Bedea; 1505A Belden HDTV; 75080 AFZ 4-S Midi 0,8/3,7; Image 720 Argosy; Telass 80 Bedea; VK6/0,8 FRLS 0,8/3,7 Percon; VPM2000 GEPCO

IEC 61169-8
 A4431
 Crimp
 Crimp
 >500

Materials / Material

CuZn39Pb3
 CuZn39Pb3
 GD-ZnAl4Cu1
 SF Cu w
 PE
 silicone / Silikon

Finish / Oberfläche

Cu1Ni2Au0,8
 Cu2Ni5
 Zn/Cu6Ni6
 Ni5

75 Ω
 typ.: 1 GHz - 36 dB; 2 GHz - 31 dB; 3 GHz - 29 dB
 ≤ 0,5 kV_{eff} / 50 Hz
 1,5 kV_{eff} / 50 Hz
 ≥ 5 GΩ
 ≤ 20 mΩ
 ≤ 5 mΩ

-40°C / +75°C
 2002/95/EC

2011	Datum/ date	Name/ name	Gewicht/ weight (g)	Oberfläche/ surface (mm ²)	Werkstoff/ material
	gez./ drawn	18.01.	JA		
	gepr./ appr.	25.01.2011	BJ		Oberfläche/ finish
	Norm/ stand.				
Maßstab/ scale	Benennung/ title				
2:1	BNC Straight Plug BNC-Kabelstecker				
untol. Maße/ dim. without tolerances according to	Untert./doc. type	Zeichnungsnr./ drawing no.		 Maße/ dimensions: mm	
	K	J01002A0082			
a	22793	19.04.11	JA	Original : DIN A4 Blatt/ sheet 1 von/ of 1	
Änd./ rev. Index	Änderungsmittellung/ revision code	Datum/ date	Name/ name	Ersatz für/ replaces EWB00063-80	