

Blanking plug CQC-28H

FESTO

Part number: 194590



Data sheet

Feature	Value
Maritime classification	See certificate
Type code	CQC
Mounting position	Any
Pack size	1
Design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar ... 7 bar
Temperature-dependent operating pressure	-0.95 bar ... 15 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
For use in the food industry	See supplementary material information
Ambient temperature	-25 °C ... 70 °C
Product weight	22 g
Pneumatic connection 1	Push-in sleeve CQ-28
Pneumatic connection 2	Push-in sleeve CQ-28
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Blanking plug material	POM