


START DOWNLIGHT IP44 225

START Downlight 225 IP44 DALI 2350Lm 840
0030339



Product features

- Ceiling recessed LED downlight IP44 (from the front), with only 65mm product depth and 225mm cutout. Supplied with DALI Tridonic push dim driver with loop in - out option (2800671). Ideal replacement for 2x26W CFL downlights. The polycarbonate diffuser allows for a wider light distribution and increased spacings between luminaires. Die-cast aluminium body, 2350LM, 23W, 102lm/W, 4000K, Driver Current: 650mA, CRI80, 74° beam angle, IP44 from the front, IK07, (HxW) 65x225mm, Class 2, 220-240V. Meets TP(a) requirements.




PRODUCT OVERVIEW

Product name	START Downlight 225 IP44 DALI 2350Lm 840
Technology	LED
Cap/Base	N/A
Housing	Aluminium
Mount	Ceiling recessed mounting
General application	Hospitality, Logistics & Industry, Office
ETIM Class	EC001744
E-number FI	4278169
Warranty	5 years
Fixture luminous flux (lm)	2350
Luminous flux (lm)	2350
Luminaire efficacy (lm/W)	102
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Beam Angle (°)	74
Glare control	< 25
Photobiological Risk Group	RG0
Total power consumption (W)	23
Electrical protection	Class II
Control gear type	LED driver constant current
Dimmable	Yes
Dimming method	DALI
Minimum dimming level (%)	1
LED Flickering Rate	Ultra low (5% or less)
Housing colour	RAL 9003 - Signal white
IP rating	IP44/20
IK rating	IK07
Product EAN number	5410288303390

START DOWNLIGHT IP44 225

START Downlight 225 IP44 DALI 2350Lm 840
0030339

PHOTOMETRY



TECHNICAL DRAWINGS

