

Parallel rest sets

ORION®

Application:

For parallel support of workpieces in machine vices, on machine tools or on marking-off plates.

Execution:

- Steel.
- The different dimensions create a multitude of combination possibilities.
- Height tolerance within a pair: 0.01 mm.
- Hardened and ground.
- In pairs, tolerance IT 5, nominal width in accordance with DIN ISO 2768-1, tolerance class M.
- Ref. no. 26256010, nominal dimensional tolerance $H + W \pm 0.02$ mm in accordance with (DIN ISO 2768-1 tolerance class M).
- Ref. no. 26256020, nominal dimension tolerance at height 14-30 mm ± 0.02 mm, at height 32-50 mm ± 0.03 mm.

Delivery:

1 set of 14 pairs in wooden box.



Art. no.	26256 010
Brand	ORION
Manufacturer Part Number	26256010
Parallel rest length	150 mm
Parallel rest width	10 mm
Parallel rest height	14 mm, 16 mm, 18 mm, 20 mm, 22 mm, 24 mm, 26 mm, 28 mm, 30 mm, 32 mm, 35 mm, 40 mm, 45 mm, 50 mm
Nominal tolerance, height 14-30 mm	± 0.02 mm
Pair tolerance	0.01 mm
Gross Weight	11.400 kg
Product Group	264

EAN

4039247170210