



Pre-Crimped Leads

Molex's range of pre-crimped leads offers a simple, cost-effective solution for prototyping, pre-production and mass production requirements. These leads are offered in female-to-female and male-to-male configurations in lengths of 75.00 to 450.00mm

Features and Advantages

Pre-crimped and fully tested cables	Decrease time to market
Available in 75.00 to 450.00mm lengths	Works well for all prototype and pre-production requirements
Leads crimped on both ends	Allows for wire-to-wire applications and when cut in half, wire-to-board applications
UL listed cables	Assures high-quality approved materials
Available for most popular Molex families	Helps customers choose the right connector before investing in application tooling




C-Grid III



CLIK-Mate




DuraClik



KK



LINK 396



Mega-Fit




MicroClasp



Micro-Fit 3.0



Micro-Lock Plus



Milli-Grid




Mini-Fit



Mini-Lock




MLX




MultiCat




Nano-Fit




PicoBlade



Pico-Clasp



Pico-EZmate



Pico-Lock



Pico-SPOX




Sabre




Sherlock



SL



Standard .062"



Standard .093"



Ultra-Fit

Product Family	Order Number	Length	Connector A	Connector B	Wire Size	Wire/Cable Type
C-Grid	797582022	150.00mm	Female	Female	22 AWG	UL 1061
	797582023	300.00mm	Female	Female	22 AWG	UL 1061
CLIK-Mate	797581011	300.00mm	Female	Female	24 AWG	UL 1061
	797581012	150.00mm	Female	Female	28 AWG	UL 1061
	797581013	300.00mm	Male	Male	28 AWG	UL 1061
	797581014	150.00mm	Male	Male	24 AWG	UL 1061
	797581015	300.00mm	Male	Male	24 AWG	UL 1061
DuraClik	797581008	150.00mm	Female	Female	26 AWG	UL 1061
	797581009	300.00mm	Female	Female	26 AWG	UL 1061
KK	797580007	150.00mm	Female	Female	22 AWG	UL 1061
	797580011	300.00mm	Female	Female	22 AWG	UL 1061
	797580015	300.00mm	Male	Male	22 AWG	UL 1061
	797582024	300.00mm	Female	Female	24 AWG	UL 1007
L1NK 396	797582145	150.00mm	Female	Female	18 AWG	UL 1051
	797582146	300.00mm	Female	Female	18 AWG	UL 1051
Mega-Fit	797582037	150.00mm	Female	Female	16 AWG	UL 1015
	797582038	300.00mm	Female	Female	16 AWG	UL 1015
	797582039	150.00mm	Female	Female	12 AWG	UL 1015
	797582040	300.00mm	Female	Female	12 AWG	UL 1015
Micro-Clasp	797581001	150.00mm	Female	Female	24 AWG	UL 1007
	797581002	300.00mm	Female	Female	24 AWG	UL 1007
Micro-Fit 3.0	797580002	150.00mm	Female	Female	20 AWG	UL 1061
	797580004	150.00mm	Female	Female	20 AWG	UL 1061
	797580010	300.00mm	Female	Female	20 AWG	UL 1061
	797580012	300.00mm	Female	Female	20 AWG	UL 1061
Micro-Lock Plus	797582143	150.00mm	Female	Female	26 AWG	UL 1061
	797582144	300.00mm	Female	Female	26 AWG	UL 1061
	797581148	150.00mm	Female	Female	26 AWG	UL 1061
	797581149	300.00mm	Female	Female	26 AWG	UL 1061
Milli-Grid	797581095	150.00mm	Female	Female	24 AWG	UL 1061
	797581096	300.00mm	Female	Female	24 AWG	UL 1061
Mini-Fit	797580001	150.00mm	Female	Female	18 AWG	UL 1061
	797580005	150.00mm	Male	Male	18 AWG	UL 1061
	797580009	300.00mm	Female	Female	18 AWG	UL 1061
	797580013	300.00mm	Male	Male	18 AWG	UL 1061
Mini-Lock	797582147	150.00mm	Female	Female	22 AWG	UL 1061
	797582148	300.00mm	Female	Female	22 AWG	UL 1061
MLX	797582029	150.00mm	Male	Male	18 AWG	UL 1015
	797582030	300.00mm	Male	Male	18 AWG	UL 1015
	797582031	150.00mm	Female	Female	18 AWG	UL 1015
	797582032	300.00mm	Female	Female	18 AWG	UL 1015
Multicat	797582059	150.00mm	Male	Male	8 AWG	UL 1199
	797582060	300.00mm	Male	Male	9 AWG	UL 1199
	797582061	150.00mm	Male	Male	12 AWG	UL 1199
	797582062	300.00mm	Male	Male	12 AWG	UL 1199
	797582063	150.00mm	Male	Male	16 AWG	UL 1199
	797582064	300.00mm	Male	Male	16 AWG	UL 1199
	797582065	150.00mm	Female	Female	8 AWG	UL 1199
	797582066	300.00mm	Female	Female	8 AWG	UL 1199
	797582067	150.00mm	Female	Female	12 AWG	UL 1199
	797582068	300.00mm	Female	Female	12 AWG	UL 1199
	797582069	150.00mm	Female	Female	16 AWG	UL 1199
Nano-Fit	797582070	300.00mm	Female	Female	16 AWG	UL 1199
	797582129	150.00mm	Female	Female	20 AWG	UL 1061
	797582130	300.00mm	Female	Female	20 AWG	UL 1061
	797582139	150.00mm	Female	Female	20 AWG	UL 1061
PicoBlade	797582140	300.00mm	Female	Female	20 AWG	UL 1061
	797581059	150.00mm	Female	Female	28 AWG	UL 1061
	797581060	300.00mm	Female	Female	28 AWG	UL 1061
	797581061	150.00mm	Female	Female	28 AWG	UL 1061
	797581062	150.00mm	Female	Male	28 AWG	UL 1061
	797581063	300.00mm	Female	Male	28 AWG	UL 1061
	797580006	150.00mm	Female	Female	26 AWG	UL 1061
	797580014	300.00mm	Female	Female	26 AWG	UL 1061

Product Family	Order Number	Length	Connector A	Connector B	Wire Size	Wire/Cable Type
Picoblade	214920-XXXX	75.00mm	Female	Female	26 AWG	UL1061
	214920-XXXX	150.00mm	Female	Female	26 AWG	UL1061
	214920-XXXX	225.00mm	Female	Female	26 AWG	UL1061
	214920-XXXX	300.00mm	Female	Female	26 AWG	UL1061
	214920-XXXX	450.00mm	Female	Female	26 AWG	UL1061
	214921-XXXX	75.00mm	Female	-	26 and 28 AWG	UL1061
	214921-XXXX	150.00mm	Female	-	26 and 28 AWG	UL1061
	214921-XXXX	225.00mm	Female	-	26 and 28 AWG	UL1061
	214921-XXXX	300.00mm	Female	-	26 and 28 AWG	UL1061
	214921-XXXX	450.00mm	Female	-	26 and 28 AWG	UL1061
	214922-XXXX	75.00mm	Male	Male	26 AWG	UL1061
	214922-XXXX	150.00mm	Male	Male	26 AWG	UL1061
	214922-XXXX	225.00mm	Male	Male	26 AWG	UL1061
	214922-XXXX	300.00mm	Male	Male	26 AWG	UL1061
	214922-XXXX	450.00mm	Male	Male	26 AWG	UL1061
	214923-XXXX	75.00mm	Male	-	26 and 28 AWG	UL1061
	214923-XXXX	150.00mm	Male	-	26 and 28 AWG	UL1061
	214923-XXXX	225.00mm	Male	-	26 and 28 AWG	UL1061
214923-XXXX	300.00mm	Male	-	26 and 28 AWG	UL1061	
214923-XXXX	450.00mm	Male	-	26 and 28 AWG	UL1061	
Pico-Clasp	797581016	150.00mm	Female	Female	28 AWG	UL 1571
	797581017	300.00mm	Female	Female	28 AWG	UL 1571
	797581018	150.00mm	Female	Female	28 AWG	UL 1571
	797581019	300.00mm	Female	Female	28 AWG	UL 1571
Pico-EZmate	797581010	300.00mm	Female	Female	28 AWG	UL 1516
Pico-Lock	797581003	150.00mm	Female	Female	24 AWG	UL 1061
	797581004	300.00mm	Female	Female	24 AWG	UL 1061
	797581005	150.00mm	Female	Female	30 AWG	UL 1571
	797581006	300.00mm	Female	Female	30 AWG	UL 1571
Pico-SPOX	797580008	150.00mm	Female	Female	24 AWG	UL 1061
	797580016	300.00mm	Female	Female	24 AWG	UL 1061
	797581007	300.00mm	Female	Female	24 AWG	UL 1061
Sabre	797582041	150.00mm	Male	Male	16 AWG	UL 1015
	797582042	300.00mm	Male	Male	16 AWG	UL 1015
	797582043	150.00mm	Female	Female	16 AWG	UL 1015
	797582044	300.00mm	Female	Female	16 AWG	UL 1015
Sherlock	797581020	150.00mm	Female	Female	26 AWG	UL 1061
	797581021	300.00mm	Female	Female	26 AWG	UL 1061
SL	797580003	150.00mm	Female	Female	22 AWG	UL 1061
Standard .062"	797582025	150.00mm	Male	Male	22 AWG	UL 1015
	797582026	300.00mm	Male	Male	22 AWG	UL 1015
	797582027	150.00mm	Female	Female	22 AWG	UL 1015
	797582028	300.00mm	Female	Female	22 AWG	UL 1015
Standard .093"	797582033	150.00mm	Male	Male	18 AWG	UL 1015
	797582034	300.00mm	Male	Male	18 AWG	UL 1015
	797582035	150.00mm	Female	Female	18 AWG	UL 1015
	797582036	300.00mm	Female	Female	18 AWG	UL 1015
Ultra-Fit	797582131	150.00mm	Female	Female	16 AWG	UL 1061
	797582132	300.00mm	Female	Female	16 AWG	UL 1061
	797582141	150.00mm	Female	Female	16 AWG	UL 1061
	797582142	300.00mm	Female	Female	16 AWG	UL 1061