

LED work lamp Silhouette

Smart light with gesture control



Application:

e.g. for testing components

Execution:

- High-performance LED in aluminium housing - 10 watt, 960 lumen, light temperature approx. 2700-5500 Kelvin, 120°
- Uniform and low-reflection illumination, glare-free and flicker-free
- Light colour can be changed and luminosity dimmed using gesture control
- Rubber-covered magnetic base
- Dust-proof and splash-proof
- Durable and robust

Delivery:

With 24 V power supply

Art. no.	56879 190
Brand	BAUER & BÖCKER
Manufacturer Part Number	900/48
Power rating	10 W
Length	750 mm
IP protection class	IP 65
Dimmable	Yes
Gross Weight	1082.000 g
Product Group	5ID



EAN

4260131239366