

Application:

For measuring lengths and length differences, e.g. concentricity, flatness, positional measurements.

Execution:

- Housing: Metal
- Clamping shank: Stainless steel
- Measuring pin: Stainless steel
- Clamping shank: Dia. 8 mm
- Dial gauge with gauge slide dia. 3.175 mm, mounted
- Clockwise
- Thread for gauge slides: M2.5

Advantage:

- Rotating dial, adjustable tolerance marks

Delivery:

In box



Art. no.	33151 010
Brand	TESA
Manufacturer Part Number	01419081
Length measuring range	5 mm
Scale value	0.01 mm
Measurement travel of one pointer revolution	0.5 mm
Outer diameter	44.5 mm
Shock protection	Yes
Material of outer ring	Metal
IP protection class	IP 67
Measurement force	0.9 N
Calibration Group	CE
Gross Weight	0.178 kg
Product Group	362

EAN

7630041151794