

Product Information

2478PJO075P60

EAN 4031582302387

Fixed castor, Fork made of pressed steel, zinc-chromatised, Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, plain bearing, plate fitting

Option:

This castor is also in electric conductive version available. Please replace PJO with YGO when ordering..



Wheel diameter	75 mm
Width of Tread	25 mm
Size of Plate	67 x 60 mm
Plate hole centres	48/40 x 48/40 mm
Plate hole	6,3 mm
Overall height	100 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	0.159 Kg / daN
Dynamic Load capacity	75 Kg / daN
Static Load capacity	150 Kg / daN
Hardness of tread	A 87 Shore

