

PSEN ma1.4-51M12/8-0.15m/PSENma1.4-03/1u**Product number:****506344**

Product version:	1.0
Approvals:	CE, cULus Listed, TÜV
Sensor principle:	magnetic
Number of N/O:	2
Connection type:	M12, 8pol. male
Switching voltage:	24 V
Type of switching voltage:	DC
Assured switching distance:	3.0 mm
Assured release distance:	12 mm
Protection type, housing:	IP67
Status indicator:	With LED
Design:	square
Width dimension:	26.4 mm
Height dimension:	37.0 mm
Depth dimension:	18.0 mm
Gross weight:	90 g
Net weight:	56 g

Ambient temperature:

-10 - 55 °C