



MATERIALS:

Screws: 4 ea. #4-40 x 1/4" Pan Head.

Finish: Cadmium plated with clear irridite dip or blue zinc.

Cover: .063 thick aluminum 1100-H14

Finish: Clear anodize per MIL-A-8625

Shielded Housing: Die cast aluminum Alloy A380, or A384.

Finish: None

RATINGS:

Operating Temperature: +150°C. (+302°F.) Max.

ORDERING INFORMATION: Model 3606

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA