

## Toledo Mirage G200

ToLEDo Mirage G200 105LM E27 SL  
0029911



### Product features

- A perfect choice for hospitality, decorative and mood lighting applications
- Unique and innovative lamp design and construction
- Low-lumen output to create the low-lit effect and gives no glare
- Low power construction: only 2.5W
- Perfect for SylPendant fixtures - a range of unique and elegant E27 lamp pendants, available in copper, brass, black and white finish
- Candlelight 2000K colour temperature creates a warm and cosy ambience
- High colour rendering - CRI80
- High quality, scratch and temperature resistant golden tinted glass envelope
- 25,000 hours of average rated life. Last 25 times longer than incandescent lamps
- Omni-directional light distribution
- Non-dimmable
- More than 100,000X switching cycles
- 3 years warranty



## PRODUCT OVERVIEW

Product name	ToLEDo Mirage G200 105LM E27 SL
Technology	LED
Watt (Rated) (W)	2.5
Type	LED exchangeable
Cap/Base	E27
Fixture rating	Open
General application	Residential & Consumer
ETIM Class	EC001959
E-number FI	4740679
Warranty	3 years
Luminous flux (lm)	105
Colour temperature (K)	2000
Light colour	Candlelight
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Photobiological Risk Group	RG0
Wattage (W)	2.5
Product Voltage (V)	230
Dimmable	No
Average life (Nominal) (h)	25000
Product EAN number	5410288299112

## DATA TABLE

### General data

Product name	ToLEDo Mirage G200 105LM E27 SL
Technology	LED
Watt (Rated) (W)	2.5

## Toledo Mirage G200

ToLEDo Mirage G200 105LM E27 SL

0029911

Type	LED exchangeable
Cap/Base	E27
Fixture rating	Open
General application	Residential & Consumer
Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
E-number FI	4740679
Warranty	3 years

### Optical data

Luminous flux (lm)	105
Luminous flux (Rated) (lm)	105
Colour temperature (K)	2000
Light colour	Candlelight
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Photobiological Risk Group	RG0
Lumen maintenance at end of nominal life (%)	70

### Electrical data

Wattage (W)	2.5
Equivalent watt (W)	12
Starting time (max) (s)	0.5
Warm-up time to 60% of full light (max) (s)	1
Product Voltage (V)	230
Lamp power factor	0.5
Control gear required	No
No. Of switching cycles before premature failures	>100000
Transformer required	No
Dimmable	No
Inrush Current (A)	0.2
Inrush Duration (µs)	8000
Lamp Energy Label (class)	G
kWh per 1000 hours burning time	3
Nominal Frequency (Hz)	50/60Hz

### Lifetime data

Lifespan L70 B50	25000
Average life (Nominal) (h)	25000
Average life (Rated) (h)	25000

### Physical data

Nominal Product Length (mm)	238
Nominal Product Diameter (mm)	200
Weight (kg)	0.38

## Toledo Mirage G200

ToLEDo Mirage G200 105LM E27 SL

0029911


### Packaging

Single packaging type	Carton
Product EAN number	5410288299112
Packaging single length / height (cm)	26.0
Packaging single width (cm)	21.0
Packaging single depth (cm)	21.0
DUN14 (outer)	15410288299119
Units per outer package	2
Packaging outer length / height (cm)	43.5
Packaging outer width (cm)	22.5
Packaging outer depth (cm)	28.5


### Safety data

Optimal operating condition (°C)	-20-40
Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Not Suitable for totally enclosed fixtures

## PHOTOMETRY



## TECHNICAL DRAWINGS



Toledo Mirage G200  
*ToLEDo Mirage G200 105LM E27 SL*  
0029911



**SYLVANIA**

0029911



**3**  
kWh/1000h




2019/2015

Toledo Mirage G200  
*ToLEDo Mirage G200 105LM E27 SL*  
0029911



0029911



**3**  
kWh/1000h



2019/2015