

## “Light strip“ LED machine light, tiltable

155, 305 or 560 mm, IP 67



### Execution:

- high-performance LED in aluminium housing
- Light temperature: cold white, approx. 5500 Kelvin, high-performance chip
- 120 degree uniform illumination, anti-glare and flicker-free, low-reflection
- connection to 24 V machine controller or to 230 V via power pack
- 2 x 43 mm rubber-coated magnets each with 85 N retention force.

### Advantage:

- Waterproof and extremely robust
- Magnetic rubber base - prevents scratches to coated surfaces
- Made in Germany - high-quality product for demanding industrial use

### Delivery:

including power pack



<b>Art. no.</b>	<b>56886 011</b>
<b>Brand</b>	BAUER & BÖCKER
<b>Manufacturer Part Number</b>	900/66
<b>Power rating</b>	5 W
<b>Length</b>	155 mm
<b>Luminous flux</b>	600
<b>IP protection class</b>	IP 67
<b>Gross Weight</b>	0.500 kg
<b>Product Group</b>	5ID

### EAN

4260131238666