

Handwheels Stainless Steel, Sheet Version

Material: Wheel body: Stainless steel sheet 1.4404 (AISI 316L).
Hub welded on. Matt blasted.
At version B/G: Handle Duroplast PF31, black,
glossy finish with axis from stainless steel 1.4404 (AISI 316L).


Hub lengths comply with DIN 950. High mechanical strength,
insensitive to blows and impacts.

Version B/A: Without thread, without cylindrical handle.

Version B/G: With revolving cylindrical handle.

Keyway available at extra charge.

Ordering Details: e.g.: Product No. 670 999 16, Handwheel, Version B/A, Diameter 160 mm



Version B/G with handle

Product No. Vers. B/A	Product No. Vers. B/G	d ₁ mm	d ₂ ^{H9} mm	d ₃ mm	b ₁ mm	l ₁ mm	l ₂ mm	Handle Ø mm	Handle Length mm	No. of Spokes pcs.	Sheet Gauge mm	Weight Vers. B/A g	Weight Vers. B/G g
670 999 16	670 994 16	160	12	30	22	37	20	26	80	4	1,5	375	490
670 999 20	670 994 20	200	14	40	22	46	24	26	80	4	2	720	850
670 999 25	670 994 25	250	17	45	30	52	28	28	90	5	2,5	1285	1450
670 999 32	670 994 32	315	19	55	35	64	33	28	90	5	2,5	2030	2170
670 999 40	670 994 40	400	24	65	40	82	38	28	90	5	3	3670	3890

Handwheels Stainless Steel, Solid Version

Material: Wheel body: Cast stainless steel 1.4308 (CF-8).
Rim turned, matt blasted.
At version B/G: Handle Duroplast PF31, black,
glossy finish. Spindle: Stainless steel 1.4305 (AISI 303).


Version B/A: Without thread, without cylindrical handle.

Version B/G: With revolving cylindrical handle.

Easy to clean.

Keyway available at extra charge.

Ordering Details: e.g.: Product No. 670 995 10, Handwheel, Vers. B/A, Diameter 100 mm



Version B/G with handle

Product No. Vers. B/A	Product No. Vers. B/G	d ₁ mm	d ₂ ^{H8} mm	d ₃ mm	b ₁ mm	l ₁ mm	l ₂ mm	Handle Ø mm	Handle Length mm	No. of Spokes pcs.	Weight Vers. B/A g	Weight Vers. B/G g
670 995 10	670 996 10	100	10	20	7	27,5	15	18	45	3	222	255
670 995 12	670 996 12	125	12	24	9	28,5	16	21	55	3	425	460
670 995 14	670 996 14	140	14	28	10	30,5	18	23	71	3	640	800
670 995 16	670 996 16	160	16	31	11	35,5	20	23	71	3	805	900
670 995 20	670 996 20	200	18	36	14	39	23	23	71	3	1442	1524
670 995 22	670 996 22	200	20	36	14	39	23	23	71	3	1400	1482

Handwheels Stainless Steel, Solid Version, similar to DIN 950

Material: Wheel body: Cast stainless steel 1.4401 (AISI 316).
Rim turned and polished.
At version B/G: Handle stainless steel 1.4404 (AISI 316 L).


Version B/A: Without thread, without handle.

Version B/G: With fixed handle.

Acid-resistant A4-quality. Easy to clean.
Dimensions almost according to DIN 950.

Keyway available at extra charge.

Ordering Details: e.g.: Product No. 670 997 10, Handwheel DIN 950, stainless steel,
Version B/A, 100 mm



Version B/G with handle

Product No. Version B/A	Product No. Version B/G	d ₁ mm	d ₂ ^{H9} mm	d ₃ mm	b ₁ mm	l ₁ mm	l ₂ mm	Handle Ø mm	Handle Length mm	No. of Spokes pcs.	Weight Vers. B/A g	Weight Vers. B/G g
670 997 10	670 998 10	100	10	25,5	14,5	33	17	16	49	3	433	480
670 997 12	670 998 12	125	12	27	15,8	35,5	18	20	62	3	659	770
670 997 14	670 998 14	140	14	29	17	38,5	19	20	62	3	865	940
670 997 16	670 998 16	160	14	31	17,5	39,5	20	25	77	3	1156	1320
670 997 20	670 998 20	200	18	37	20	44,5	24	25	77	3	1938	2060