

SIMATIC DP, CONNECTING MODULE FOR PROFINET
 INTERFACE MODULES ET 200PRO; CONNECTOR 2XRJ45 2X
 POWER PLUG PUSH PULL FOR PROFINET PN



Figure similar

Input current	
from load voltage 2L+ (without load), max.	No current consumption, only infeed current, max. 16 A with derating
from supply voltage 1L+, max.	No current consumption, only infeed current, max. 16 A with derating
Interfaces	
PROFIBUS DP	
• Transmission rate, max.	100 Mbit/s; full-duplex, PROFINET
Accessories	
Function description	IM PN, 2xRJ45, 2xPushPull interface module
belongs to product	IM154-4 PN HF
Weights	
Weight, approx.	325 g
last modified:	12.03.2015