


**NOTES:**

1. MATERIALS:  
HOOD: PBT GF UL94 V-0 BLACK  
FRONTSEALING: SILICONE VMQ BLUE  
SCREW: STAINLESS STEEL  
O-RING: NBR BLACK
2. TEMPERATURE RANGE: -30°C TO +90°C
3. RECOMMENDED TORQUE FOR SCREW:  
35Ncm (3.1 in.LB)  
MAX. TORQUE: 68Ncm (6 in.LB)
4. SINGLE PACKED

\* COMPLETELY TIGHTENED



Directive 2002/95/EC RoHS compliant

|   |                   |             |            |                                  |           |         |                            |  |         |        |
|---|-------------------|-------------|------------|----------------------------------|-----------|---------|----------------------------|--|---------|--------|
| THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND | tolerance         |             | dim. in mm |                                  | scale:    |         | 1,5:1 (1:1)                |  |         |        |
|   | ±0,3 unless       |             |            |                                  | material: |         | SEE NOTES                  |  |         |        |
|   | otherw. specified |             |            |                                  | title:    |         | WATER RESISTANT D-SUB HOOD |  |         |        |
|   | date              | name        | drawn      | 06.02.2014                       | Heinrich  | 25 POS. |                            |  |         |        |
|   | appd.             | 06.02.2014  | Huether    | JACKSREW 4-40UNC STAINLESS STEEL |           |         |                            |  |         |        |
|   | norm              |             |            |                                  |           |         |                            |  | dwg no: |        |
|   | d-old             | 15K1A1152   |            |                                  |           |         |                            |  |         | DIN-A3 |
|   | a                 | Origin      |            |                                  |           |         |                            |  |         | sh: 1  |
|   | rev.              | description | date       | name                             | part no:  |         | 15-004680                  |  |         |        |
|   |                   |             |            |                                  |           |         |                            |  |         |        |