

Hydraulic pressure cylinder RC



Execution:

- Single-acting cylinder.
- Model RC 50 with stationary thrust piece, all other cylinders with interchangeable, grooved thrust piece.
- Operating pressure of 700 bar
- With spring return mechanism.
- With scraper ring (apart from model RC 50).
- Hard-chrome-plated piston rod.
- With retaining thread on cylinder head (except mod. RC 50).

Advantage:

- Suitable for universal use.
- Retaining ring prevents piston rod from being pushed out.

Delivery:

1x ENERPAC hydraulic pressure cylinder RC 51.



Art. no.	29501 060
Brand	ENERPAC
Manufacturer Part Number	RC1010
Model	RC 1010
Max. compressive force	101 kN
Lift height	257 mm
Oil capacity	373 cm ³
Construction height, retracted	349 mm
Weight	6.4 kg
Gross Weight	6.365 kg
Product Group	258