


WP26

Air Cooled TIG Welding Torch

200A DC, 150A AC @ 60% Duty Cycle, EN60974-7 .020"-5/32" / 0.5mm to 4.0mm Electrodes



Models

SSW denotes Switched and Sheathed

Stock Code	Description
WP26-12	TIG Torch x 12.5ft (3.8m) c/w Vinyl Power Cable
WP26-12R	TIG Torch x 12.5ft (3.8m) c/w Rubber Cable
WP26-12-2	TIG Torch x 12.5ft (3.8m) c/w 2 Piece Power Cable
WP26-12SSW	TIG Torch x 12.5ft (3.8m) c/w Vinyl Power Cable, SSW
WP26-12RSSW	TIG Torch x 12.5ft (3.8m) c/w Rubber Cable, SSW
WP26-12-2SSW	TIG Torch x 12.5ft (3.8m) c/w 2 Piece Power Cable, Switch
WP26-25	TIG Torch x 25ft (7.6m) c/w Vinyl Power Cable
WP26-25R	TIG Torch x 25ft (7.6m) c/w Rubber Cable
WP26-25-2	TIG Torch x 25ft (7.6m) c/w 2 Piece Power Cable
WP26-25SSW	TIG Torch x 25ft (7.6m) c/w Vinyl Power Cable, SSW
WP26-25RSSW	TIG Torch x 25ft (7.6m) c/w Rubber Cable, SSW
WP26-25-2SSW	TIG Torch x 25ft (7.6m) c/w 2 Piece Power Cable, Switch

Alternative Torch Body

Stock Code	Description
WP26FX-	TIG Torch with Flexi Head
WP26V-	TIG Torch with Valve Head
WP26VFX-	TIG Torch with Flexi Valve Head

Collet

Stock Code	Description
10N21	Collet .020"/0.5mm Bore
10N22	Collet .040"/1.0mm Bore
10N23	Collet 1/16"/1.6mm Bore
10N24	Collet 3/32"/2.4mm Bore
10N25	Collet 1/8"/3.2mm Bore
54N20	Collet 5/32"/4.0mm Bore

Collet Body

Stock Code	Description
10N29	Collet Body .020"/0.5mm Bore
10N30	Collet Body .040"/1.0mm Bore
10N31	Collet Body 1/16"/1.6mm Bore
10N32	Collet Body 3/32"/2.4mm Bore
10N28	Collet Body 1/8"/3.2mm Bore
406488	Collet Body 5/32"/4.0mm Bore

For torch packages with alternative torch bodies please order with the above prefix.

To add a Cable Plug please refer to Page 185.

Zipper Cover Options are also available, please suffix your torch stock code with a "Z" i.e. WP26-12Z or WP26-12SZ for Switch and zipper cover.

All torches are supplied 3/8" BSP as standard.
For alternate configurations please refer to Page
131-135