


ROLINE USB 3.2 Gen 2 Type C Multiport Docking Station, 4K HDMI, 2x USB 3.2 Gen 2, 1x USB Type C PD (Power Delivery), 1x Gigabit Ethernet

Product No. 12.02.1121
Manufacturer ROLINE
Manufacturer No. 12.02.1121

roline
Designed for Professionals



The USB Type C Docking Station provides your MacBook, Ultrabook, Notebook or Laptop with a 4k capable HDMI port, 2x USB 3.0 / USB 3.2 Gen 2, 1x USB Type C PD (Power Delivery) and 1x Gigabit Ethernet!

- Plug & Play
- Aluminium housing in space grey
- Multiport Docking Station with HDMI connection, allows the expansion of a display or mirroring to another monitor, television or beamer.
- Max. Resolution: 3840x2160 at 30Hz
- Compact and flat design.

- System requirements: Windows 7/8/10 or MacOS X10.2 and higher

Connection to the mobile device:

- 1x USB Type C connector

Connections for peripheral devices:

- 1x HDMI 4K video output: Mirror or expand your screen to a TV, monitor or projector.
- 2x USB 3.0 / USB 3.2 Gen 2 Type A ports (data transfer rate up to 5Gbit/s), for connecting e.g. keyboard/mouse, USB HDD/SSD, etc.
- 1x USB 3.2 Gen 2 Type C
- 1x USB Type C PD (Power Delivery, max. 100W)
- 1x RJ45 for Gigabit Ethernet

Remark: Support of "Alternate Mode" required

Note: According to the current specifications of USB.org we have adapted the technical data of our USB 3 products. The new designation for the already known USB specifications has been changed to USB 3.2 Gen 1 (formerly USB 3.0 / USB 3.1 Gen 1) and USB 3.2 Gen 2 (formerly USB 3.1 / USB 3.1 Gen 2).

Technical specifications	
Manufacturer	ROLINE
Product group	Adapters, Terminators, Converters
Product type	Docking Station
Colour	grey
Scope of delivery	Docking Station
Side 1 connection (PC)	USB Type C
Side 2 connection (Peripherals)	2x USB 3.2 Gen 2 socket, 1x HDMI socket, 1x Gigabit Ethernet socket, 1x USB C, 1x PD
Side 1 Connector Type	USB Type C (USB-C)
Side 1 Connector Gender	Male
Side 2 Connector Type	HDMI Type A RJ-45 USB Type C (USB-C)
Side 2 Connector Gender	Female
Material	Aluminum
Height	15 mm
Width	103 mm
Depth	45 mm
Weight	83 g