

Product information

97 53 04 SB

Self-Adjusting Crimping Pliers for wire ferrules

With lateral access




- Narrow handle width and improved ergonomics
- Square compression now for wire ferrules up to 16 mm²
- Square compression for ideal contact surfaces in the clamp connection
- Suitable in particular for all twin wire ferrules up to 2 x 4 mm² or 2 x AWG 12
- For crimping wire ferrules according to DIN 46228 parts 1 + 4
- Self-adjustment to the size of wire ferrules required
- Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Handy shape and low weight provide high operation comfort
- Special quality chrome vanadium electric steel, oil-hardened

General

Article No.	97 53 04 SB
EAN	4003773030270
Pliers	burnished
Handles	with multi-component grips
Weight	420 g
Dimensions	180 x 115 x 35 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details



Application	Wire ferrules
Capacity in square millimetres	0.08 — 10 / 16 mm ²
Number of crimping positions	1
AWG	28 — 6

technical change and errors excepted



Crimping capacity can be switched over simply from 10 mm² to 16 mm².