

Roller container with vice holder plate

With 4 fully extending drawers

Version:

- Welded sheet steel structure with 4 rubber-tyred wheels, 2 of which are fixed wheels (diameter 300 mm) and 2 of which are steering rollers (diameter 200 mm), lockable
- With large folding steel tube push handle
- Top of deposit tray fitted with a ribbed rubber mat
- Tilt-proof due to built-in individual drawer pull-out lock
- Delivered without vice, please order separately (see no. 51028001 ATORN parallel vice, jaw width 100 mm)
- Vice can be attached to the upper frame of the trolley (carrier plate provided on frame)
- For suitable insert materials for drawers, see from no. 50485 060-265 and no. 50537 610-695
- Other equipment options available at extra cost: SOFT-CLOSE for drawers, see no. 50392 005, ELECTRONIC CODE combination lock, see no. 50392 010



Art. no.	50282 187
Number of drawers	4 PCS
Pullout type	Full extension
Number of loading surfaces	1 PCS
Drawer front height	2 x 60 mm, 1 x 90 mm, 1 x 120 mm
Height	930/800 mm
Width	570 mm
Depth	680 mm
Draw width (inner dimension)	450 mm
Drawer depth (inner dimension)	600 mm
Load-carrying capacity per drawer	70 kg
With single pull-out safety brake	Yes
Central locking	Yes
Lock type	DOM® locking system
With sliding handle	Yes
Load-carrying capacity	910 kg
Number of fixed rollers	2 PCS
Number of steering rollers	2 PCS
Number of wheel adjusters	2 PCS
Material of wheel	Solid rubber
Wheel diameter	300/200 mm
Material	Sheet steel
Body colour	Optional
Colour of front	Optional
Surface	Powder-coated

EAN-Code

4039247969593