


Cable glands for hazardous areas

EXIOS⁺ A2F
Metr.


Material	Brass
Seal	Silicone, VMQ
Clamping insert	PA 6
Protection	IP 66, 67 and 68 (5 bar)
Operating Temperature	-60° C – 105° C (-76° F – 221° F)



Advice:
- Stainless Steel on request



AG	Size	∅k A1 mm	GL mm	H max. mm	∅ mm	D mm	Number	Number Nickel plated brass
M 16 x 1,5	20 - 1	6 - 12	16	36,5	22	27	1.608.1600.50	1.608.1603.50
M 20 x 1,5	20 - 1	6 - 12	16	36,5	22	27	1.608.2000.50	1.608.2003.50
M 20 x 1,5	20 - 2	9 - 16	16	41	24	29	1.608.2000.51	1.608.2003.51
M 25 x 1,5	20 - 3	12,5 - 20,5	16	48	30	35	1.608.2500.50	1.608.2503.50
M 32 x 1,5	25	16,9 - 26	16	48,5	36	42	1.608.3200.50	1.608.3203.50
M 40 x 1,5	32	22 - 33	16	54	46	52	1.608.4000.50	1.608.4003.50
M 50 x 1,5	40	28 - 41	16	60	55	64	1.608.5000.50	1.608.5003.50
M 63 x 1,5	50	40 - 52,6	16	67	65	73	1.608.6300.50	1.608.6303.50
M 75 x 1,5	63	51 - 65,3	16	72	80	90	1.608.7500.50	1.608.7503.50
NPT 3/8"	20 - 1	6 - 12	16	35,6	22	27	1.608.3800.70	1.608.3803.70
NPT 1/2"	20 - 1	6 - 12	20	35,6	22/24	27	1.608.1200.70	1.608.1203.70
NPT 1/2"	20 - 2	9 - 16	20	39,7	24	29	1.608.1200.71	1.608.1203.71
NPT 3/4"	20 - 3	12,5 - 20,5	20,5	47,5	30	35	1.608.3400.70	1.608.3403.70
NPT 1"	25	16,9 - 26	25	47,8	36	42	1.608.1000.70	1.608.1003.70
NPT 1 1/4"	32	22 - 33	26	51,1	46	52	1.608.5400.70	1.608.5403.70
NPT 1 1/2"	40	28 - 41	26,5	56,8	55	64	1.608.6400.70	1.608.6403.70
NPT 2"	50	40 - 52,6	27	65,4	65	73	1.608.2000.70	1.608.2003.70
NPT 2 1/2"	63	51 - 61	40	70,3	80	90	1.608.5200.70	1.608.5203.70
NPT 3"	75	62 - 78	41,5	76,2	95	107	1.608.3000.70	1.608.3003.70