

SRGC clamping holder, positive, right

For copy, longitudinal face lathing with RC indexable insert

ATORN[®]

Application

For longitudinal turning with RC indexable insert

Version

- Precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces



Art. no.	17850 519
ISO name	SRGC R/L 2525 M10
Shaft height	25 mm
Shank width	25 mm
Length	150 mm
Length of head	20.7 mm
Programming size	32 mm
Suitable for indexable inserts	RC.. 1003..
Tool design	Left

EAN-Code

4050293563160