

# ESD PLUG-IN SCREWDRIVER SETS



Practical tool rolls made from dissipative material are equipped with double-ended screw-driver-blades and ESD handle with brass clamping sleeve, suitable for hexagon blades of A / F 4 mm

Blade: chrome vanadium, hexagon material, A / F 4 x 120 mm, hardened over its full length, matt chrome-plated, black tip



**4-920**  
Interchangeable screwdriver set with ESD handle, 9-pcs.

**Content:** ESD-handle  
3 Slotted blades 1,5 / 3,0 mm, 2,0 / 3,5 mm, 2,5 / 4,0 mm  
2 Cross-recess blades PH 000 / PH 00, PH 0 / PH 1  
3 TORX-blades T 5 / T 6, T 7 L / T 8 L, T 9 L / T 10 L (from T 7 with hole)

**Weight:** 190 g



**4-960**  
Interchangeable screwdriver set with ESD handle, 11-pcs.

**Content:** ESD-handle  
2 Slotted blades 1,5 / 3,0 mm, 2,5 / 4,0 mm  
2 Cross-recess blades PH 000 / PH 00, PH 0 / PH 1  
4 TORX-blades T 3 / T 4, T 5 / T 6, T 7 L / T 8 L, T 9 L / T 10 L (from T 7 with hole) 2 Tri Wing / Four Wing Blades TW 1 / FW 1, TW 2 / FW 2

**Weight:** 210 g



4-960

# ESD SCREWDRIVERS

with special square pattern handle from impact-resistant, dissipative, black plastic

**Blade:** chrome-vanadium, fully hardened, matt chromium-plated, black tip

**Handle:** impact resistant, dissipative, black plastic, electrostatic discharge according to DIN EN 100015/1

## Slotted screwdrivers



No.	Blade length mm	Blade width mm	Thickness mm	Handle size mm	Weight g
4-632	100	4.0	0.8	92 x 21	40
4-633	125	5.5	1.0	100 x 23	65



4-633

## Cross-recess screwdrivers PH



No.	Size	Blade length mm	Blade Ø mm	Handle size mm	Weight g
4-652	1	80	4.5	92 x 21	40
4-653	2	100	6.0	100 x 23	75



4-653

## Cross-recess screwdrivers PZ



4-662	1	80	4.5	92 x 21	40
4-663	2	100	6.0	100 x 23	70

## Tri Wing screwdrivers



6-641	TW 0	70	4.5	92 x 21	42
6-642	TW 1	70	4.5	92 x 21	42
6-643	TW 2	70	4.5	92 x 21	42
6-644	TW 3	70	4.5	92 x 21	42
6-645	TW 4	70	6.0	92 x 21	53
6-646	TW 5	70	6.0	92 x 21	54



4-644