



10
JAHRE
YEARS
GARANTIE
WARRANTY

ANSMANN FL4500AC

- ANSMANN Luminary BASE work floodlight with 50 W SMD LEDs and a lighting power of up to 4.500 lumens
- Extremely bright and homogeneously illuminated light for working in indoor and outdoor areas
- Integrated 500 cm long H07RN-F rubber cable for flexible use outdoors such as on construction sites, for moderate mechanical stresses.
- Splash-proof (IP65) - can be used indoors and out
- Robust aluminium and ABS housing – extremely shock-resistant
- Very pleasant LED light with a colour temperature of 5000K (daylight)
- Versatile use thanks to the sturdy adjustment bracket - the adjustable support can be adjusted up to 80°, and the light head a full 360°!
- The spotlight is very compact when folded up thanks to the adjustable bracket - the carry handle also enables it to be comfortably carried to the desired place of use

INFORMATION

Product name	FL4500AC
Part No.	1600-0403
EAN-Code	4013674172658
Customs tariff number	94054239000
Product content	FL4500AC, operating instructions

Packing + Product	328 × 87 × 340 mm / 2792 g
Packing Unit	4 (373 × 343 × 360 mm)

