



Datenblatt - Fiche technique - Data sheet

**11.04.5852**




ROLINE HDMI High Speed Kabel mit Ethernet, ST-ST, schwarz / silber, 3,0 m

ROLINE Câble HDMI High Speed avec Ethernet, noir/argent, 3,0 m

ROLINE HDMI High Speed Cable + Ethernet, M/M, black /silver, 3.0 m

# HDMI 19 M

# HDMI 19 M




Part No.	Cable L	Braid L
11.04.5850	1000±20 mm	1000±20 mm
11.04.5851	2000±20 mm	2000±20 mm
11.04.5852	3000±20 mm	3000±20 mm
11.04.5853	5000±20 mm	5000±20 mm

### Specification :

- 1 Cable UL20276, (1P\*30AWG+AL+D+MYLAR)\*5+4C\*30AWG+MYLAR+AL+D+B, Black PVC, OD: 6.5 mm, RoHS
- 2 Braid Black Cotton Braid, RoHS
- 3 Connector HDMI 19P M, Shell: Gold Plated 1u", Pin: Golded 1u", RoHS
- 4 Solder 0.8 mm Tin Line, RoHS
- 5 Tube 1 Black Tube OD: 0.8 mm, L=11 mm, RoHS
- 6 Tube 2 Black Tube OD: 2.5 mm, L=6 mm, RoHS
- 7 Inner Mold LD PE, RoHS
- 8 Tape High Temperature Resistant, L=55 mm W=18 mm, RoHS
- 9 Copper Foil Package Copper Foil and Spot Welding, L=55 mm W=22 mm, RoHS
- 10 Metal Shell Dark Grey Aluminum Shell (Print HDMI LOGO), RoHS
- 11 Outer Mold PVC: 60P Black, RoHS
- 12 Dust Cover HDMI M Dust Cover

### Pin Assignment



Rev.	Date	Contents of Change	Designer	Tol±										Approve	Check	Draw	Design	Product Name	ROLINE SILVER HDMI High Speed Cable+Ethernet, M/M					
				Range	Pla	Met	Ins	Por	Cab	Pac	Gas	Dis	Allen	Allen		Philip	Drawing Date	Product No.	11.04.5850 / 11.04.5851 / 11.04.5852 / 11.04.5853		R00			
△				0~6	0.1	0.1	0.1	0.2	0.5	1	0.5	0.2									2017-03-22			
△				6~30	0.1	0.1	.15	.25	1	1	0.5	.25												
△				30~80	0.1	.15	0.2	0.3	2	1.5	1	0.3												
△				80~180	.15	.15	.25	0.3	2	2	1	.45												
△				180~315	.15	0.2	0.3	0.4	2.5	2	1	0.6												
△				315~800	0.2	0.3	0.4	0.5	3	3	2	1.1												



Scale 1:1 Unit mm