

Tubular Inside Micrometers

SERIES 133 — Single-Rod Type

Technical Data

Accuracy: Refer to the list of specifications.
Graduation: 0.01mm or .001"


Optional Accessories

---- : Setting ring (See page C-29.)



FEATURES

- With locking clamp.
- Zero point can be readjusted by rotating the micrometer head sleeve. A key wrench is supplied.
- Clear, crisp graduations on the satin-chrome finished micrometer head.
- Carbide-tipped measuring faces.
- Supplied in fitted plastic case. Over 200mm / 8" supplied in wooden case.



SPECIFICATIONS

Metric Individual		
Range	Order No.	Accuracy
50 - 75mm	133-143	±3μm
75 - 100mm	133-144	±4μm
100 - 125mm	133-145	±5μm
125 - 150mm	133-146	±5μm
150 - 175mm	133-147	±5μm
175 - 200mm	133-148	±5μm
200 - 225mm	133-149	±5μm
225 - 250mm	133-150	±6μm
250 - 275mm	133-151	±6μm
275 - 300mm	133-152	±6μm
300 - 325mm	133-153	±7μm
325 - 350mm	133-154	±7μm
350 - 375mm	133-155	±7μm
375 - 400mm	133-156	±8μm
400 - 425mm	133-157	±8μm
425 - 450mm	133-158	±8μm
450 - 475mm	133-159	±9μm
475 - 500mm	133-160	±9μm
500 - 525mm	133-161	±9μm
525 - 550mm	133-162	±10μm
550 - 575mm	133-163	±10μm
575 - 600mm	133-164	±10μm
600 - 625mm	133-165	±11μm
625 - 650mm	133-166	±11μm
650 - 675mm	133-167	±11μm
675 - 700mm	133-168	±12μm

Metric Individual		
Range	Order No.	Accuracy
700 - 725mm	133-169	±12μm
725 - 750mm	133-170	±12μm
750 - 775mm	133-171	±13μm
775 - 800mm	133-172	±13μm
800 - 825mm	133-173	±13μm
825 - 850mm	133-174	±14μm
850 - 875mm	133-175	±14μm
875 - 900mm	133-176	±14μm
900 - 925mm	133-177	±15μm
925 - 950mm	133-178	±15μm
950 - 975mm	133-179	±15μm
975 - 1000mm	133-180	±16μm

Inch Individual		
Range	Order No.	Accuracy
2" - 3"	133-223	±.00015"
3" - 4"	133-224	±.0002"
4" - 5"	133-225	±.00025"
5" - 6"	133-226	±.00025"
6" - 7"	133-227	±.00025"
7" - 8"	133-228	±.00025"
8" - 9"	133-229	±.00025"
9" - 10"	133-230	±.0003"
10" - 11"	133-231	±.0003"
11" - 12"	133-232	±.0003"

Tubular Inside Micrometers

SERIES 133



Metric Micrometer set		
Range	Order No.	Included in set
50 - 150mm (4 pcs. set)	133-901	• 133-143, 133-144, 133-145, 133-146 • with fitted case
50 - 300mm (10 pcs. set)	133-902	• 133-143, 133-144, 133-145, 133-146, 133-147, 133-148, 133-149, 133-150, 133-151, 133-152 • with fitted case

Inch Micrometer set		
Range	Order No.	Included in set
2" - 6" (4 pcs. set)	133-903	• 133-223, 133-224, 133-225, 133-226 • with fitted case
2" - 12" (10 pcs. set)	133-904	• 133-223, 133-224, 133-225, 133-226, 133-227, 133-228, 133-229, 133-230, 133-231, 133-232 • with fitted case

DIMENSIONS

