

## Angular milling cutter 90°

For indexable milling insert WNEX 0806..

**ATORN®**

### Application

Powerful angular milling cutter with particularly economic, double-sided indexable insert with 6 cutting edges. Flexible use for multiple machining steps, such as face, angular, trim and groove milling.

### Version

- Wear-resistant, nickel-plated version
- With internal cooling

### Advantage

- 6 cutting edges on double-sided indexable insert
- Special chip shape geometry for low power consumption
- Large plate thickness for optimum process reliability
- Optimised plane cutting edge for high surface quality



<b>Art. No.</b>	<b>16020 525</b>
<b>Cutting edge diameter</b>	125 mm
<b>Length</b>	63 mm
<b>Bore diameter</b>	40 mm
<b>max. ap</b>	6 mm
<b>Number of cutting edges</b>	11 PCS

### EAN-Code

4050293540024