

## Electronic dial gauge

ID-U

Mitutoyo

### Application:

For measuring, e.g. in devices on production machines

### Execution:

- ABSOLUTE system for reliable measurement
- ON/OFF
- LCD digit size 8.5 mm
- Digimatic
- Counting direction can be switched
- Narrow construction with 25 mm measuring range

### Advantage:

- Long battery life



<b>Art. no.</b>	<b>32019 311</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	575-121
<b>Length measuring range</b>	25.4 mm
<b>Digit increment</b>	0.01 mm
<b>Min./max. measurement force</b>	0-0.8 N
<b>Error limit</b>	0.02 mm
<b>Data transmission type</b>	DIGIMATIC
<b>IP protection class</b>	IP 42
<b>Functions</b>	ABS function, On/Off, Reversal of counting direction
<b>Absolute function</b>	Yes
<b>Automatic switch-off</b>	No
<b>Dynamic measurement</b>	No
<b>Preset function</b>	No
<b>Shank diameter</b>	8 mm
<b>Tolerance value entry</b>	No
<b>Manual tolerance markers</b>	No
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Colour reading classification</b>	No
<b>Rechargeable battery/battery capacity</b>	155 mAh
<b>Battery voltage</b>	1.55 V
<b>Weight of rechargeable battery/battery</b>	0.002 kg
<b>Battery designation</b>	1,5 V SR44
<b>Rotating housing</b>	No
<b>Combined indicator for figure/scale reading</b>	No
<b>Reversible counting direction</b>	Yes
<b>Digit height</b>	8.5 mm
<b>Design</b>	Metric
<b>Display</b>	Digital
<b>Calibration Group Description</b>	Dial gauge
<b>Calibration Group</b>	CE
<b>Gross Weight</b>	0.260 kg
<b>Product Group</b>	3MA

### EAN

4946368131276