


START Waterproof Slim

START Waterproof Slim 1200 IP65 4600lm 840
0046370



Product features

- START Waterproof Slim is a LED integrated polycarbonate housing luminaire with easy to access electrical terminal through bayonet lock end caps and tool-free electrical connection due to push-in terminal. Flexible installation as mounting brackets can be positioned freely on the luminaire. 35W; 4600lm; High efficiency with 131lm/W and 100,000 hours lifespan L70B50. SDCM < 5; IP65; IK08; Class I; 1207mm x 70mm x 69mm.




PRODUCT OVERVIEW

Product name	START Waterproof Slim 1200 IP65 4600lm 840
Technology	LED
Cap/Base	N/A
Housing	PC Polycarbonate
Mount	Ceiling surface mounting
General application	Logistics & Industry
ETIM Class	EC002892
E-number FI	4357076
Warranty	5 years
Fixture luminous flux (lm)	4600
Luminaire efficacy (lm/W)	131
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Beam Angle (°)	120
Photobiological Risk Group	RG0
Total power consumption (W)	35
Electrical protection	Class I
Control gear type	LED driver constant current
Dimmable	No
Dimming method	N/A
Housing colour	Grey
IP rating	IP65
IK rating	IK08
Product EAN number	5410288463704

PHOTOMETRY

START Waterproof Slim

START Waterproof Slim 1200 IP65 4600lm 840
0046370



TECHNICAL DRAWINGS

