




Material: Messing vernickelt  
 max. Betriebsdruck: 18 bar  
 max. Betriebstemperatur: 200 °C  
 verwendbare Schläuche: PA, PE, PU



11.514-8-E

**Gerade Aufschraubverschraubung, Innengewinde**

Typen Nr.	Artikel Nr.	ØD	G	I	L			O-Ring
11.518-6-E	114766	6/4	G 1/8	8,0	25,0	12	14	ohne
11.518-8-E	114767	8/6	G 1/8	8,0	25,0	14	14	ohne
11.514-6-E	114764	6/4	G 1/4	11,0	29,0	12	17	ohne
11.514-8-E	114765	8/6	G 1/4	11,0	29,0	14	17	ohne
11.514-10-E	114763	10/8	G 1/4	11,0	30,5	16	17	ohne
11.538-6-E	114769	6/4	G 3/8	11,5	29,5	12	20	ohne
11.538-8-E	114770	8/6	G 3/8	11,5	29,5	14	20	ohne
11.538-10-E	114768	10/8	G 3/8	11,5	31,0	16	20	ohne
11.512-8-E	114762	8/6	G 1/2	14,0	33,0	14	24	ohne
11.512-10-E	114761	10/8	G 1/2	14,0	34,5	16	24	ohne