


E12341



Connecting cable with socket

ADOAH040MSS0030C04



Application

Special feature	Free from silicone; Halogen-free; Gold-plated contacts; Screened cable; Drag chain suitability
Free from silicone	yes

Electrical data

Operating voltage	[V]	< 50 AC / < 60 DC
Protection class		III
Max. current load total	[A]	4

Operating conditions

Ambient temperature	[°C]	-25...85
Note on ambient temperature		21 days: ...120
Protection		IP 67

Mechanical data

Weight	[g]	1479
Dimensions	[mm]	28 x 15 x 38
Materials		TPU
Material nut		diecast zinc
Drag chain suitability		yes
Drag chain suitability	bending radius	min. 10 x cable diameter

Remarks

Pack quantity	1 pcs.
---------------	--------

E12341



Connecting cable with socket

ADOAH040MSS0030C04

Electrical connection


Cable: 30 m, PUR, Halogen-free, black, Ø 5 mm, shielded; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x M12, angled; Moulded body: TPU; Locking: diecast zinc; Contacts: gold-plated; Tightening torque: 0.7...0.9 Nm;
Shielded connection cable: screen not connected



Connection



Core colours :

BK =	black
BN =	brown
BU =	blue
WH =	white