

PORTWEST®

PRODUCT SPECIFICATION & TECHNICAL DATA

A110 - Polka Dot Glove

Collection: General Handling

Range: Gloves

Materials: Polyester, PVC

Dipping: PVC

Inner Pack: 12

Outer Carton: 216

Product information

By combining enhanced grip with excellent dexterity, the Polka Dot Glove performs well in dry conditions. Seamless 13 gauge knitted liner with PVC dotted palm.



General Handling

The General Handling and Grip Glove category is still one of the most popular collections within the Portwest Hand Protection Range. A carefully selected range of coatings, including Latex, Nitrile, Polyurethane and PVC, provides a broad range of styles suited to a diverse range of tasks.

Gloves

A wide and increasing range of Hand Protection styles is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

AS/NZS 2161 .2
AS/NZS 2161 .3
ANSI/ISEA 105: 2016 CUT Level (A1)
EN388:2016 +A1:2018 - (2.1.4.X.X)
EN 420



Features

- CE certified
- PVC dotted palm for enhanced grip
- 100% breathable seamless liner
- Performs well in dry conditions
- Seamless 13 gauge liner
- Excellent for jobs requiring high dexterity
- ANSI abrasion level 1
- ANSI cut level A1

| | Range |
|---------------|---------------|
| Blue on White | XS/6 - XXL/11 |
| Black/Red | S/7 - XL/10 |

PORTWEST®

PRODUCT SPECIFICATION & TECHNICAL DATA

A110 - Polka Dot Glove

Commodity Code: 6116108000

Test House

CTC (Notified Body No.: 0075)

4, rue Hermann Frenkel

Cedex 07, France

Cert No: 0075/2085/162/08/19/2432

CARTON DIMENSIONS/WEIGHT

| Item | Colour | Len | Wid | Hgt | Weight (Kg) | Cubic (m ³) | EAN13 | DUN14 |
|------------|--------|------|------|------|-------------|-------------------------|---------------|----------------|
| A110BKRXXS | Black | 56.0 | 27.0 | 37.0 | 0.0500 | 0.0559 | 5036108331505 | 15036108819826 |
| A110BKRXS | Black | 56.0 | 27.0 | 37.0 | 0.0500 | 0.0559 | 5036108331499 | 15036108819819 |
| A110BKRS | Black | 56.0 | 27.0 | 37.0 | 0.0500 | 0.0559 | 5036108293391 | 15036108768933 |
| A110BKRM | Black | 56.0 | 27.0 | 37.0 | 0.0500 | 0.0559 | 5036108293384 | 15036108768926 |
| A110BKRL | Black | 56.0 | 27.0 | 37.0 | 0.0500 | 0.0559 | 5036108293377 | 15036108768919 |
| A110BKRXL | Black | 56.0 | 27.0 | 37.0 | 0.0500 | 0.0559 | 5036108293407 | 15036108768940 |