

Single-tooth milling cutter HSSE Co 5

1 cutter, uncoated

ORION[®]

Application:

For milling, plunging and contour milling NF metals and plastics.



Version:

- HSSE Co 5
- Straight shank pursuant to DIN 6535 HA
- Sharp-edged
- Uncoated

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
						60	186	30	35	25	32	77	30						

Art. no.	15007 080
Cutting material	HSSE Co5
Surface	Uncoated
Type	W
Number of cutting edges	1 PCS
Twist angle	40°
Tool holding device	HA parallel shank
Overall length	Normal
Cutting edge diameter	8 mm
Cutting edge length	14 mm
Length	80 mm
Shaft diameter	8 mm
fz aluminium	0.018 mm

EAN-Code

4039247083121