

## Nuts

For T-grooves




### Application:

For clamping in T-grooves.

### Execution:

- Ref. no. 010- 130 tempered, strength class 10
- Ref. no. 220- 310 tempered, strength class 10, long form



<b>Art. no.</b>	<b>26195 050</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	80044
<b>Type</b>	standard
<b>Nominal dimension of groove</b>	14 mm
<b>Slot nut width</b>	13.7 mm
<b>Thread dimension</b>	M12
<b>Length</b>	22 mm
<b>Height</b>	16 mm
<b>Slot nut height</b>	8 mm
<b>DIN</b>	508
<b>Gross Weight</b>	0.033 kg
<b>Product Group</b>	260

### EAN

4020772080044