

Product information

03 05 140

Combination Pliers

DIN ISO 5746

- With gripping zones for flat and round material, suitable for versatile use
- With cutting edges for soft and hard wire
- Long cutting edges for thicker cables
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 60 HRC
- Special tool steel, forged, multi stage oil-hardened



General

| | |
|-----------------|----------------------------|
| Article No. | 03 05 140 |
| EAN | 4003773039730 |
| Pliers | chrome-plated |
| Head | chrome-plated |
| Handles | with multi-component grips |
| Weight | 139 g |
| Dimensions | 140 x 57 x 18 mm |
| Standard | DIN ISO 5746 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|--|----------------------|
| Cutting capacities medium hard wire (diameter) | Ø 2.8 mm |
| Cutting capacities hard wire (diameter) | Ø 1.8 mm |
| Cutting capacity copper cable, multiple-stranded | Ø 9.0 mm |
| Cutting capacity copper cable, multiple-stranded | 10.0 mm ² |

technical change and errors excepted