

5

4

3

2


1

SPECIFICATION



Mating Cycles	500
Filter type	C
Capacitance	1000pf±20%
Working Voltage	100V
Current rating	7.5 A
Insulation Resistance	>1GΩ



Minimum Insertion Loss

FREQUENCY (MHz)	ATTENUATION dB
5	1dB
10	3dB
50	12dB
100	20dB
500	34dB
1000	30dB



Solder bucket for AWG 20



				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, female, straight 9 Poles, with turned solder bucket, fixing hole	Ma?Ms Lab/ Scale 1.5:1
			Detail.	8-JUL-02	CV			
			Insp.					
32802	11/07/05	JMDR	Stand.				TB 09641117230	Blatt/ Page 1 / 1
31894	29/04/04	AF						
31058	8-JUL-02	CV						
Mod.	Dat.	Name	HARTING EURL F-95972 Paris					

D

C

B

A